



SCHOPPER-RIEGLER FREENESS TESTER

For determination of the degree of refining of
pulp-suspensions in °SR.



Digital model

MODELS

MANUAL MODEL

Sealing cone is lifted by an inbuild weight

PNEUMATIC MODEL

Sealing cone is lifted pneumatically

DIGITAL MODEL

- Digital display of °SR-degree and 4 drainage times
- Sensor for measuring the freeness
- RS 232-port for readout of a drainage graph

Optional: system with a built-in balance instead of the sensor

MOST IMPORTANT BENEFITS

- ✓ Housing and drainage part made of stainless steel
- ✓ ISO-nozzle, according to standards
- ✓ Single button operation (fulfills the safety regulations)

PRODUCT DESCRIPTION

The drainage chamber and the hydraulic cylinder are mounted on a robust stainless steel frame. The filling chamber is sealed below with a special screen, which leads to the spreader cone. The cone has two outlet openings. A sealing cone closes the filling chamber against the spreader cone and prevents the suspension from escaping before the test actually starts. Depending on the mechanism fitted, the sealing cone lifts either pneumatically or mechanically at the speed acc. standard.

The digital version is equipped with a sensor that shows the Schopper-Riegler freeness ($^{\circ}\text{SR}$) on a display module, to an accuracy of 0.1 $^{\circ}\text{SR}$.

TEST DESCRIPTION

The pulp sample (2 g pulp), prepared with the standardised disintegrator (see page 12), is poured into the closed filling chamber. The sealing cone lifts automatically once the start button is pressed (for the digital version) or when the handle is operated (manual and pneumatic version). The suspension is drained through the screen, leaving a fibre pad, and the filtrate drains into the separating chamber. The water volume fraction drained through the side discharge pipe is collected in a $^{\circ}\text{SR}$ measuring beaker. In the manual and pneumatic versions the freeness is readable from the Schopper-Riegler scale on the measuring beaker, and in the digital version the freeness is shown on the display module.

TECHNICAL DATA

DEVICE/INSTRUMENT

- Housing and drainage part made of stainless steel
- Chamber with sieve, sealing cone and separating funnel mounted on the frame
- Single button operation (fulfills the safety regulations)
- ISO-nozzle according to standards
- Included into delivery:
- 2 pcs $^{\circ}\text{SR}$ -measuring beakers
- C-spanner for sieve changing
- Compatible with ProbeNet

INSTALLATION REQUIREMENTS


| | |
|-----------------------|---|
| Electrical connection | 100 – 230 V / 50 – 60 Hz (with digital model only) |
| Water connection | No |
| Compressed air | 4 – 6 bar (with pneumatic model only) |

APPLICABLE STANDARDS

- ISO 5267-1
- ect.



2 pieces $^{\circ}\text{SR}$ -measuring beakers included into delivery



Drainage graph



Pneumatic and manual model